


Archer Materials (ASX:AXE)

- ^{12}CQ Quantum Program

9th April 2025



ARCHER

Spin Coherence in Carbon Nanospheres

ARTICLE



Received 10 Oct 2015 | Accepted 14 Jun 2016 | Published 18 Jul 2016

DOI: 10.1038/ncomms12232



OPEN

Room temperature manipulation of long lifetime spins in metallic-like carbon nanospheres

Bálint Náfrádi¹, Mohammad Choucair², Klaus-Peter Dinse³ & László Forró¹



Advanced positioning and lithography for nanoscale device fabrication





Archer is developing novel carbon materials with long room temperature T_2 spin coherence lifetimes, useful for a wide range of quantum applications.




Archer's Quantum Carbon Film

Quantum film deposition



- Films are currently deposited using laboratory tools.
- Deposition is a CVD-based process. We expect scalability to full wafers.

Electron spin coherence time


$$T_2 \approx 830 \text{ ns}$$

At room temperature

With development
predicting a 2-3 times
increase of T_2
– well beyond $1 \mu s$

- We are exploiting the long spin lifetime for quantum device applications:
 - Primary focus: spin qubits.
 - Other: highly sensitive quantum magnetometers and magnetic microscopes.

Archer has developed a carbon film material with spin coherence lifetimes of $\sim 1 \mu s$.
The deposition process is compatible with full wafer scale manufacture.

Film Processing and Device Fabrication


Carbon film deposited on a range of substrates, including silicon and SiO_2



- Photo- or e-beam lithography.
- Standard RIE etching.




Spin confinement device




- CVD-like process.
- Carbon-based precursors.
- Good run-to-run and chip-to-chip uniformity.
- Low impurity levels .



Nanoscale quantum transport device




- Photo- or e-beam lithography.
- Standard RIE etching.
- Metallization.




We are using traditional fab processing to fabricate nanoscale devices for development work and prototype devices.

Single Electron Transistors – Coulomb Blockade





- Addition energy (E_{add}) of ~ 400 meV – matching a temperature of 80 Kelvin.
- Excited states (E^*), result of C=C bond stretching:
 - Coupling of ~ 200 meV.
 - Suggests very strong electron-vibrational mode coupling.




Building devices around nanoscale islands of our carbon film has allowed demonstration of Coulomb blockade and the first part of a spin readout structure.

Micro-resonators – Spin Detection and Control



Avoided-crossing $\rightarrow$ quantum hybridization when resonator frequency is close to the spin transition frequency

Effective coupling vs temperature



Decrease in spin polarisation with increasing temperature

Clarity of observed signal indicates high electron spin densities.

Micro-resonator coupling, as demonstrated, will provide a mechanism for spin control.

Chip-based Spin Detection

X-Band Single Chip Integrated Pulsed Electron Spin Resonance Microsystem

Reza Farsi,* Nergiz Sahin Solmaz,* Mattéo Maury, and Giovanni Boero




Cite This: *Anal. Chem.* 2024, 96, 14516–14523




Read Online

Chip design has been manufactured on SiGe BiCMOS, HEMT and standard CMOS technology platforms



Pulsed electron spin resonance allow direct measurements of electron spin lifetime




Archer has developed chip-based ESR microsystem demonstrating efficient detection of $\sim 10^7$ spins, within its carbon spin material.


Qubit Roadmap

Qubit components

1. Confinement (CNO device)




2. Control (global/local)




3. Readout (graphene SET)

Elzerman et al, Nature 430 (2004)




Work in progress




Work will be extended on devices built around nanodots of carbon.
Targeting an Elzerman qubit architecture demonstration in 2026.

Sensing Applications - Magnetometry

Sensor dimension vs sensitivity




Proposed carbon-dot magnetic microscope




Array of lithographically defined spin single electron transistors (SSETs) would allow an extremely sensitive, high spatial resolution magnetic microscope

Incumbent technologies




1. Magnetic Force Microscopy –
Can only scan surfaces



2. Scanning SQUID microscopy –
Requires cryogenic temperature

3. Nitrogen-vacancy in diamond –
Requires optical excitation and readout



Archer's carbon films could be used for a differentiated magnetic microscope → non-destructive, high throughput, room temperature.

Archer Materials – Quantum Program

- We are developing quantum technology in differentiated carbon-based materials that have attractive quantum properties even at elevated temperatures.
 - Our focus is qubit technology for quantum computing.
 - There is the possibility to develop quantum sensors e.g. highly sensitive room-temperature magnetometers.
- Our long electron spin lifetime carbon materials can be deposited as films via a fab-friendly CVD-like process.
- Targeting qubit demonstration by mid-2026.
 - Demonstrated quantum transport through single electron device structure.
 - Demonstrated coupling to micro resonators for control.
- We are seeking external partnerships and opportunities for industry and academic research organizations to support this work.





hello@archerx.com.au



<https://twitter.com/archerxau?lang=en>



<https://www.linkedin.com/company/archerxau>

Sign up to our Newsletter: <http://eepurl.com/dKosXI>

ASX Code: AXE

ACN: 123 993 233

The Board of Archer authorised this announcement to be given to ASX.

archerx.com.au



ARCHER